








 SCENAR Pro (2007)	 SCENAR Pro (2008)	 SCENAR Pro + (2008)	 SCENAR Pro 2009	 SCENAR Pro+ 2009	 RITM SCENAR Expert 2003
Status	Available by request only	Available by request only	Available by request only	Current model	Current model	Current model
Country of origin /Manufacturer	Russia RITM OKB ZAO	Russia RITM OKB ZAO	Russia RITM OKB ZAO	Russia RITM OKB ZAO	Russia RITM OKB ZAO	The Netherlands RITMEDIC (Under license from RITM OKB ZAO)
Diagnostic modes	DIAG 0 DIAG 1	DIAG 0 DIAG 1	DIAG 0 DIAG 1,2,3	DIAG 0 DIAG 1	DIAG 0 DIAG 1,2,3	DIAG 0 DIAG 1,2,3
Damping	N/A	SC1,2,3,4,and VAR	SC1,2,3,4,and VAR	SC1,2,3,4,and VAR	SC1,2,3,4,and VAR	SC1,2,3,4,and VAR
Amplitude modulation	"3 : 1"	"1 : 1", "2 : 1", "3 : 1", "4 : 1", "5 : 1"	"1 : 1", "2 : 1", "3 : 1", "4 : 1", "5 : 1"	"1 : 1", "2 : 1", "3 : 1", "4 : 1", "5 : 1"	"1 : 1", "2 : 1", "3 : 1", "4 : 1", "5 : 1"	"1 : 1", "2 : 1", "3 : 1", "4 : 1", "5 : 1"
"BEE" function	Manual setting	Manual setting	Manual setting	Manual setting	Manual setting	Pre-set
Frequency modulation FM	30 - 120Hz, cycle - 8sec	30 - 120Hz, cycle - 8sec	30 - 120Hz, cycle - 8sec	30 - 120Hz, cycle - 8sec	30 - 120Hz, cycle - 8sec	30 - 120Hz, cycle - 8sec
Swing mode	N/A	N/A	SW1, SW2, SW3, SW4	SW1, SW2, SW3, SW4	SW1, SW2, SW3, SW4	SW1
Influencing impulse frequencies	15, 60, 120, 350Hz	15...350Hz	15...350Hz	15...350Hz	15...350Hz	15...350Hz
Intensity (the number of impulses in a packet)	1	1...8 Can be applied to multiple Frequencies	1...8 Can be applied to multiple Frequencies	1...8 Can be applied to multiple Frequencies	1...8 Can be applied to multiple Frequencies	1...8 Can only be applied to one frequency

	 SCENAR Pro (2007)	 SCENAR Pro (2008)	 SCENAR Pro + (2008)	 SCENAR Pro 2009	 SCENAR Pro+ 2009	 RITM SCENAR Expert 2003
Function of musical modulations frequency	N/A	N/A	N/A	By custom request	By custom request	N/A
Service menu functions						
Screen Backlight function timer	OFF, 1 sec, 2 sec, 3sec, 5 sec, 10 sec, 30 sec	OFF, 1 sec, 2 sec, 3sec, 5 sec, 10 sec, 30 sec	OFF, 1 sec, 2 sec, 3sec, 5 sec, 10 sec, 30 sec	OFF, 1 sec, 2 sec, 3sec, 5 sec, 10 sec, 30 sec	OFF, 1 sec, 2 sec, 3sec, 5 sec, 10 sec, 30 sec	OFF, 4 sec
Display contrast	10 settings	10 settings	10 settings	10 settings	10 settings	N/A
Standby mode	ON, 5min, 10min, 20min	ON, 5min, 10min, 20min	ON, 5min, 10min, 20min	ON, 5min, 10min, 20min	ON, 5min, 10min, 20min	N/A
Display contrast	10 settings	10 settings	10 settings	10 settings	10 settings	N/A
Volume Settings	Mute,1,2,3	Mute,1,2,3	Mute,1,2,3	Mute,1,2,3	Mute,1,2,3	N/A
Certificates	ISO 9001 ISO 13843 European Directive 93/42/EEC ARTG ID: 140659	ISO 9001 ISO 13843 European Directive 93/42/EEC ARTG ID: 140659	ISO 9001 ISO 13843 European Directive 93/42/EEC ARTG ID: 140659	ISO 9001 ISO 13843 European Directive 93/42/EEC ARTG ID: 140659	ISO 9001 ISO 13843 European Directive 93/42/EEC ARTG ID: 140659	European Directive 93/42/EEC ARTG ID: 164651